

Garant GRIDLINE

Top-mounted cabinet with Viewing window swing doors, Height: 500mm



Order data

Order number	940013 500
GTIN	4062406067144
Item class	9GI

Description

Version:

Equipped cabinet in 20×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	20 kg
Electronic locking system can be retrofitted	yes

Usable height	345 mm
Width	500 mm
Height	500 mm
Number of shelves	1
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Handle positioning	bottom
ComfortClose	no
Depth	500 mm
Cabinet fronts	Viewing window swing door
Depth in G	20
Width in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm	940640 200
Storage shelf for cabinet / compartment width in G 20	940550 20
Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm	940640 150
Slide handle for GridLine Type GP11	914226 GP11

Inclined shelf for cabinet / compartment width in G 20	940560 20
Storage shelf slotted for cabinet / compartment width in G 20	940552 20
Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm	940640 125
Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm	940640 100
Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm	940640 75
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F