

Garant GRIDLINE

Base cabinet with drawer, Viewing window swing doors, 16×16G, Height: 900mm**Order data**

Order number	940023 900
GTIN	4062406067250
Item class	9GI

Description**Version:**

Equipped cabinet in 20×20G, with drawers 16×16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. Drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Usable height	745 mm
Height	900 mm
Drawer/pull-out shelf load capacity	75 kg
ComfortClose	no
Depth	500 mm
Number of drawers	1
Width	500 mm
Handle positioning	top
Number of shelves	1
Drawer runner extension (partial/full extension)	100 %
Weight	39 kg
Cabinet fronts	Viewing window swing door
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Drawer usable depth in G	16
Drawer usable width in G	16
Depth in G	20
Drawer usable width	400 mm
Drawer usable depth	400 mm
Width in G	20
Drawer usable area in G	16×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable width × usable depth in G	16×16G
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 20G Drawer front height 300 mm	940640 300
Inclined shelf for cabinet / compartment width in G 20	940560 20
Storage shelf slotted for cabinet / compartment width in G 20	940552 20
Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm	940640 125
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Basic lighting set for GridLine cabinets withswing doors for cabinet height 900/1000 mm	940501 900/1000
Slide handle for GridLine Type GP11	914226 GP11
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Non-slip mats set for drawers,5 pieces Dimension in G 16X16	951885 16X16
Cover made of laminated wood Dimension in G 20X20	951985 20X20
Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm	940640 75
Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm	940640 100
Ribbed rubber mat for drawers Dimension in G 16X16	951910 16X16
Storage shelf for cabinet / compartment width in G 20	940550 20
Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm	940640 150
Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm	940640 200

Cover made of bamboo Dimension in G 20X20

951980 20X20