

Garant GRIDLINE

**Base cabinet with Plain sheet metal swing doors, Height: 800mm****Order data**

Order number	940041 800
GTIN	4062406067342
Item class	9GI

**Description****Version:**

Equipped cabinet in 30×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Electronic locking system can be retrofitted	yes
--	-----

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Height	800 mm
ComfortClose	no
Handle positioning	top
Width	750 mm
Weight	39 kg
Usable height	645 mm
Cabinet fronts	Plain sheet metal swing door
Depth	500 mm
Number of shelves	1
Depth in G	20
Width in G	30
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Inclined shelf for cabinet / compartment width in G 30	940560 30
Cover made of laminated wood Dimension in G 30X20	951985 30X20
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 750/800 mm	940510 750/800

Slide handle for GridLine Type GP11	914226 GP11
Cover made of bamboo Dimension in G 30X20	951980 30X20
Storage shelf for cabinet / compartment width in G 30	940550 30
Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 30	958146 30
Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm	940501 750/800
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30