

Garant GRIDLINE

Base cabinet with Plain sheet metal swing doors, Height: 900mm**Order data**

Order number	940041 900
GTIN	4062406067359
Item class	9GI

Description**Version:**

Equipped cabinet in 30×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
---	--------

Cabinet fronts	Plain sheet metal swing door
Width	750 mm
Handle positioning	top
Depth	500 mm
Electronic locking system can be retrofitted	yes
Usable height	745 mm
Height	900 mm
Weight	42 kg
ComfortClose	no
Number of shelves	1
Width in G	30
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Storage shelf for cabinet / compartment width in G 30	940550 30
Cover made of bamboo Dimension in G 30X20	951980 30X20
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F

Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Slide handle for GridLine Type GP11	914226 GP11
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 900 mm	940510 900
Cover made of laminated wood Dimension in G 30X20	951985 30X20
Inclined shelf for cabinet / compartment width in G 30	940560 30
Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 30	958146 30