

Garant **GRIDLINE****Base cabinet with drawer, Plain sheet metal swing doors, 26×16G, Height: 800mm****Order data**

Order number	940061 800
GTIN	4062406067540
Item class	9GI

**Description****Version:**

Equipped cabinet in 30×20G, with drawers 26×16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. drawers with front height 125 mm.

**Supplied with:**

Cabinet with shelves and drawers.

**Colour:**

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

ComfortClose	no
Cabinet fronts	Plain sheet metal swing door
Electronic locking system can be retrofitted	yes
Number of shelves	1
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Weight	44 kg
Width	750 mm
Drawer/pull-out shelf load capacity	75 kg
Handle positioning	top
Depth	500 mm
Height	800 mm
Drawer runner extension (partial/full extension)	100 %
Usable height	645 mm
Number of drawers	1
Depth in G	20
Width in G	30
Drawer usable width in G	26
Drawer usable depth	400 mm
Drawer usable depth in G	16
Drawer usable width	650 mm
Drawer usable area in G	26×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×16G

Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 750/800 mm	940501 750/800
Storage shelf for cabinet / compartment width in G 30	940550 30
Ribbed rubber mat for drawers Dimension in G 26X16	951910 26X16
Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 30	958146 30
Drawer for swing-door cabinets, Width 30G Drawer front height 200 mm	940641 200
Non-slip mats set for drawers, 5 pieces Dimension in G 26X16	951885 26X16
Cover made of bamboo Dimension in G 30X20	951980 30X20
Drawer for swing-door cabinets, Width 30G Drawer front height 75 mm	940641 75
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Drawer for swing-door cabinets, Width 30G Drawer front height 100 mm	940641 100
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 750/800 mm	940510 750/800
Drawer for swing-door cabinets, Width 30G Drawer front height 150 mm	940641 150
Inclined shelf for cabinet / compartment width in G 30	940560 30
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Mat for drawers Dimension in G 26X16	951830 26X16

Cover made of laminated wood Dimension in G 30X20	951985 30X20
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets,Width 30G Drawer front height 125 mm	940641 125
Drawer for swing-door cabinets,Width 30G Drawer front height 300 mm	940641 300
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F