

Garant GRIDLINE

Base cabinet with drawer, Viewing window swing doors, 26×16G, Height: 1000mm**Order data**

Order number

940063 1000

GTIN

4062406067632

Item class

9GI

Description**Version:**

Equipped cabinet in 30×20G, with drawers 26×16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Handle positioning	top
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Height	1000 mm
Drawer runner extension (partial/full extension)	100 %
Electronic locking system can be retrofitted	yes
Cabinet fronts	Viewing window swing door
ComfortClose	no
Number of drawers	1
Drawer/pull-out shelf load capacity	75 kg
Depth	500 mm
Number of shelves	2
Weight	53 kg
Usable height	845 mm
Width	750 mm
Width in G	30
Drawer usable width in G	26
Drawer usable depth	400 mm
Drawer usable width	650 mm
Depth in G	20
Drawer usable depth in G	16
Drawer usable area in G	26×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable width × usable depth in G	26×16G
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 30	958146 30
Cover made of laminated wood Dimension in G 30X20	951985 30X20
Drawer for swing-door cabinets, Width 30G Drawer front height 200 mm	940641 200
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Mat for drawers Dimension in G 26X16	951830 26X16
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm	940510 1000/1250
Drawer for swing-door cabinets, Width 30G Drawer front height 150 mm	940641 150
Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Non-slip mats set for drawers, 5 pieces Dimension in G 26X16	951885 26X16
Drawer for swing-door cabinets, Width 30G Drawer front height 100 mm	940641 100
Inclined shelf for cabinet / compartment width in G 30	940560 30
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Storage shelf for cabinet / compartment width in G 30	940550 30
Drawer for swing-door cabinets, Width 30G Drawer front height 125 mm	940641 125

Drawer for swing-door cabinets,Width 30G Drawer front height 75 mm	940641 75
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Ribbed rubber mat for drawers Dimension in G 26X16	951910 26X16
Drawer for swing-door cabinets,Width 30G Drawer front height 300 mm	940641 300
Cover made of bamboo Dimension in G 30X20	951980 30X20
Slide handle for GridLine Type GP11	914226 GP11