

Garant GRIDLINE

**Base cabinet with drawer, Viewing window swing doors, 26×16G, Height: 2000mm****Order data**

Order number	940063 2000
GTIN	4062406067663
Item class	9GI

**Description****Version:**

Equipped cabinet in 30×20G, with drawers 26×16G. Mountings for shelves at 25mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. drawers with front height 125 mm.

**Supplied with:**

Cabinet with shelves and drawers.

**Colour:**

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Cabinet fronts	Viewing window swing door
ComfortClose	no
Width	750 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Depth	500 mm
Height	2000 mm
Handle positioning	centre
Number of shelves	3
Weight	96 kg
Electronic locking system can be retrofitted	yes
Drawer runner extension (partial/full extension)	100 %
Usable height	1845 mm
Drawer/pull-out shelf load capacity	75 kg
Number of drawers	3
Drawer usable depth	400 mm
Width in G	30
Drawer usable width	650 mm
Drawer usable width in G	26
Drawer usable depth in G	16
Depth in G	20
Drawer usable area in G	26×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable width × usable depth in G	26×16G
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Drawer for swing-door cabinets,Width 30G Drawer front height 100 mm	940641 100
Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 30	958146 30
Mat for drawers Dimension in G 26X16	951830 26X16
Inclined shelf for cabinet / compartment width in G 30	940560 30
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Slide handle for GridLine Type GP11	914226 GP11
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30
Drawer for swing-door cabinets,Width 30G Drawer front height 150 mm	940641 150
Basic lighting set for GridLine cabinets withswing doors for cabinet height 2000 mm	940501 2000
Storage shelf for cabinet / compartment width in G 30	940550 30
Drawer for swing-door cabinets,Width 30G Drawer front height 300 mm	940641 300
Extended lighting set for GridLine cabinets withSwing doors, width 30G for cabinet height 2000 mm	940510 2000
Drawer for swing-door cabinets,Width 30G Drawer front height 125 mm	940641 125
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Non-slip mats set for drawers,5 pieces Dimension in G 26X16	951885 26X16
	940552 30

Storage shelf slotted for cabinet / compartment width in G 30

Ribbed rubber mat for drawers Dimension in G 26X16

951910 26X16

Drawer for swing-door cabinets,Width 30G Drawer front height 75 mm

940641 75

Drawer for swing-door cabinets,Width 30G Drawer front height 200 mm

940641 200