

Garant GRIDLINE

**Top-mounted cabinet with drawer, Viewing window swing doors, 26×16G,
Height: 750mm****Order data**

Order number	940073 750
GTIN	4062406067694
Item class	9GI

Description**Version:**

Equipped cabinet in 30×20G, with drawers 26×16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door. drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Drawer runner extension (partial/full extension)	100 %
Depth	500 mm
Width	750 mm
Drawer/pull-out shelf load capacity	75 kg
Usable height	595 mm
Cabinet fronts	Viewing window swing door
Height	750 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Number of drawers	1
Number of shelves	1
Electronic locking system can be retrofitted	yes
Handle positioning	bottom
Weight	43 kg
ComfortClose	no
Drawer usable depth	400 mm
Drawer usable width	650 mm
Drawer usable depth in G	16
Depth in G	20
Drawer usable width in G	26
Width in G	30
Drawer usable area in G	26×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable width × usable depth in G	26×16G
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Storage shelf for cabinet / compartment width in G 30	940550 30
Mat for drawers Dimension in G 26X16	951830 26X16
Non-slip mats set for drawers,5 pieces Dimension in G 26X16	951885 26X16
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 750/800 mm	940510 750/800
Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Inclined shelf for cabinet / compartment width in G 30	940560 30
Drawer for swing-door cabinets,Width 30G Drawer front height 150 mm	940641 150
Drawer for swing-door cabinets,Width 30G Drawer front height 75 mm	940641 75
Basic lighting set for GridLine cabinets with swing doors for cabinet height 750/800 mm	940501 750/800
Drawer for swing-door cabinets,Width 30G Drawer front height 100 mm	940641 100
Drawer for swing-door cabinets,Width 30G Drawer front height 200 mm	940641 200
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets,Width 30G Drawer front height 125 mm	940641 125
Ribbed rubber mat for drawers Dimension in G 26X16	951910 26X16
	940552 30

Storage shelf slotted for cabinet / compartment width in G
30

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F

Drawer for swing-door cabinets, Width 30G Drawer front
height 300 mm

940641 300