

Garant GRIDLINE

Base cabinet with Plain sheet metal swing doors, Height: 750mm



Order data

Order number	940081 750
GTIN	4062406068004
Item class	9GI

Description

Version:

Equipped cabinet in 40×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, **powder-coated**.

Doors RAL 7016 anthracite, **powder coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Handle positioning	top

Number of shelves	1
Usable height	595 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width	1000 mm
ComfortClose	no
Depth	500 mm
Weight	45 kg
Cabinet fronts	Plain sheet metal swing door
Height	750 mm
Width in G	40
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Storage shelf for cabinet / compartment width in G 40	940550 40
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 40	958146 40
Slide handle for GridLine Type GP11	914226 GP11

Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Cover made of bamboo Dimension in G 40X20	951980 40X20
Inclined shelf for cabinet / compartment width in G 40	940560 40
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 750/800 mm	940511 750/800
Basic lighting set for GridLine cabinets with swing doors for cabinet height 750/800 mm	940501 750/800
Cover made of laminated wood Dimension in G 40X20	951985 40X20