

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 1250mm



Order data

| | |
|--------------|---------------|
| Order number | 940083 1250 |
| GTIN | 4062406068110 |
| Item class | 9GI |

Description

Version:

Equipped cabinet in 40×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, **powder-coated**.

Doors RAL 7016 anthracite, **powder coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|----------------|---------------------------|
| Cabinet fronts | Viewing window swing door |
|----------------|---------------------------|

| | |
|---|--|
| Height | 1250 mm |
| Electronic locking system can be retrofitted | yes |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg |
| Weight | 65 kg |
| Number of shelves | 2 |
| ComfortClose | no |
| Handle positioning | top |
| Width | 1000 mm |
| Usable height | 1095 mm |
| Depth | 500 mm |
| Depth in G | 20 |
| Width in G | 40 |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Door opening angle | 250 degrees |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet | Base cabinet |
| Type of product | Cabinet with shelves |

Accessories

| | |
|---|--------------|
| Shelf clip set for GridLine cabinets 20 pieces Type F | 940559 F |
| Cover made of laminated wood Dimension in G 40X20 | 951985 40X20 |
| Storage shelf slotted for cabinet / compartment width in G 40 | 940552 40 |
| Storage shelf for cabinet / compartment width in G 40 | 940550 40 |

| | |
|--|------------------|
| Inclined shelf for cabinet / compartment width in G 40 | 940560 40 |
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 40 | 958146 40 |
| Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 1000/1250 mm | 940511 1000/1250 |
| Basic lighting set for GridLine cabinets with swing doors for cabinet height 1250 mm | 940501 1250 |
| Storage shelf 200 kg for cabinet / compartment width in G 40 | 940590 40 |
| Cover made of bamboo Dimension in G 40X20 | 951980 40X20 |