

Garant GRIDLINE

## Top-mounted cabinet with Viewing window swing doors, Height: 500mm



### Order data

Order number	940093 500
GTIN	4062406068172
Item class	9GI

### Description

#### Version:

Equipped cabinet in 40×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

#### Supplied with:

Cabinet with storage shelves.

#### Colour:

Body RAL 7035 light grey, **powder-coated**.

Doors RAL 7016 anthracite, **powder coated**.

#### Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Width	1000 mm
Depth	500 mm
Cabinet fronts	Viewing window swing door
Weight	32 kg

Number of shelves	1
ComfortClose	no
Handle positioning	bottom
Usable height	345 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Height	500 mm
Electronic locking system can be retrofitted	yes
Depth in G	20
Width in G	40
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

## Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Storage shelf for cabinet / compartment width in G 40	940550 40
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Slide handle for GridLine Type GP11	914226 GP11
Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Inclined shelf for cabinet / compartment width in G 40	940560 40

