

Garant GRIDLINE

Drawer for swing-door cabinets, Width 20G, 16×16G, Drawer front height: 125mm**Order data**

Order number	940640 125
GTIN	4062406066604
Item class	9GI

Description**Version:**

Drawers for installation in GridLine cabinets. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

Suitable for:

Cabinets No. 940001 – 940103; No. 940111 – 940113, No. 940801 – 940843.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Unsuitable for installation in sliding door cabinets.

Technical description

Weight	14 kg
Drawer/pull-out shelf load capacity	75 kg
Usable height	100 mm
Usable depth in G	16
Usable width in G	16
Application range	Cabinet with shelves
Usable width	400 mm

Usable depth	400 mm
with individual drawer release system	no
Material thickness	0.9 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	16×16G
Type of product	Drawer

Accessories

Non-slip mats set for drawers,5 pieces Dimension in G 16X16	951885 16X16
Ribbed rubber mat for drawers Dimension in G 16X16	951910 16X16
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75