


Garant GRIDLINE

Drawer for swing-door cabinets, Width 40G, 36×16G, Drawer front height: 125mm



Order data

Order number	940642 125
GTIN	4062406068349
Item class	9GI

Description

Version:

Drawers for installation in GridLine cabinets. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

Suitable for:

Cabinets No. 940001 – 940103; No. 940111 – 940113, No. 940801 – 940843.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Unsuitable for installation in sliding door cabinets.

Technical description

Usable height	100 mm
Drawer/pull-out shelf load capacity	75 kg
Usable depth in G	16
Weight	14 kg
Usable width in G	36
Application range	Cabinet with shelves
Usable depth	400 mm
Usable width	900 mm

with individual drawer release system	no
Material thickness	0.9 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×16G
Type of product	Drawer

Accessories

Mat for drawers Dimension in G 36X16	951830 36X16
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Non-slip mats set for drawers,5 pieces Dimension in G 36X16	951885 36X16
Ribbed rubber mat for drawers Dimension in G 36X16	951910 36X16