


Garant GRIDLINE

Rack panel for plain sheet metal doors, Type: L**Order data**

Order number	940705 L
GTIN	4062406068455
Item class	9GI

Description**Version:**

Of sheet metal for mounting hooks and open storage bins. The rack panels are screwed to the inside of swing doors, using the fastenings provided. **Only for cabinets with plain sheet metal swing doors of minimum size 750 mm wide and 1000 mm high.** Cabinets with a height of 2000 mm can take 2 panels per swing door. Load capacity per door: 10 kg. With □ 9×9 mm at 37 mm intervals for mounting accessories for perforated panels (Group 95).

Colour:

Anthracite RAL 7016 **powder-coated.**

Note:

- **Open storage bins and wide projecting tools cannot be inserted at the height of storage shelves.**
- **Suitable only for GridLine cabinets with swing doors.**

Technical description

Height	800 mm
Hoffmann perforated panel grid interval	9×9 mm
Width	250 mm

Thickness	28 mm
Material thickness	0.9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Perforated rear panel