

Garant GRIDLINE

Base cabinet with Roller shutter, Height: 2000mm**Order data**

Order number	940849 2000
GTIN	4062406068509
Item class	9GI

Description**Version:**

Empty cabinet in 40×20G. Suitable drawers: 36×14G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.
Roller shutter of anodised aluminium profiles, colour not configurable.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95.
According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	20
Depth	500 mm
Weight	81 kg

Width	1000 mm
Handle positioning	centre
Cabinet fronts	Roller shutter
ComfortClose	no
Usable height	1845 mm
Width in G	40
Electronic locking system can be retrofitted	yes
Height	2000 mm
Type of cabinet	Base cabinet
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Storage shelf 200 kg for cabinet / compartment width in G 40	940590 40
Inclined shelf for cabinet / compartment width in G 40	940560 40
Storage shelf for cabinet / compartment width in G 40	940550 40
Storage shelf slotted for cabinet / compartment width in G 40	940552 40