

Garant GRIDLINE

Base cabinet with Roller shutter, Height: 1000mm



Order data

Order number	940089 1000
GTIN	4062406068479
Item class	9GI

Description

Version:

Equipped cabinet in 40×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, **powder-coated**.

Roller shutter of anodised aluminium profiles, colour not configurable.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Cabinet fronts	Roller shutter
----------------	----------------

Height	1000 mm
Electronic locking system can be retrofitted	yes
Usable height	845 mm
Number of shelves	2
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width	1000 mm
Weight	56 kg
Depth	500 mm
Handle positioning	bottom
ComfortClose	no
Width in G	40
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Cover made of bamboo Dimension in G 40X20	951980 40X20
Drawer for sliding door cabinets,Width 40G Drawer front height 125 mm	940652 125
Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm	940652 75

Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm	940652 200
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
Cover made of laminated wood Dimension in G 40X20	951985 40X20
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Slide handle for garment lockers without cylinder insert	914221
Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm	940652 300
Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm	940652 150
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm	940652 100
Inclined shelf for cabinet / compartment width in G 40	940560 40
Storage shelf for cabinet / compartment width in G 40	940550 40