

Garant GRIDLINE

Base cabinet with Roller shutter, Height: 2000mm



Order data

Order number	940089 2000
GTIN	4062406068486
Item class	9GI

Description

Version:

Equipped cabinet in 40×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, **powder-coated**.

Roller shutter of anodised aluminium profiles, colour not configurable.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
--	-----

Depth	500 mm
Cabinet fronts	Roller shutter
Handle positioning	bottom
ComfortClose	no
Weight	102 kg
Width	1000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width in G	40
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Slide handle for garment lockers without cylinder insert	914221
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Drawer for sliding door cabinets, Width 40G Drawer front height 125 mm	940652 125
Storage shelf for cabinet / compartment width in G 40	940550 40
	940652 75

Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm

Inclined shelf for cabinet / compartment width in G 40

940560 40

Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm

940652 100

Storage shelf200 kg for cabinet / compartment width in G 40

940590 40

Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm

940652 200

Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm

940652 150

Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm

940652 300