

Garant**Shelving cabinet without doors, Height: 1000mm****Order data**

Order number	944009 1000
GTIN	4062406068530
Item class	9GI

Description**Version:**

Mountings for storage shelves at 25-mm intervals.

Equipped shelf cabinet in 30×11G.

Fitted with:

Number of storage bins: 12 × No. 963321 size SB6; 12 × No. 963321 size SB5; 12 × No. 963321 size SB4

Supplied with:

Cabinet with shelves and open storage bins.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

- **For single open storage bins see No 963321.**
- **For individual storage shelves see No. 944061, 944065.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	845 mm
Height	1000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Width	750 mm
Number of shelves	4
Weight	47 kg
Cabinet fronts	open
Depth	275 mm
Width in G	30
Depth in G	11
Material thickness	0.9 mm
Cabinet housing internal load capacity	500 kg
Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Racking cupboard

Accessories

Storage shelves for shelving cabinets, depth 11 G for cabinet width in G 30	944061 30
Stepped shelves for shelving cabinets, depth 11 G for cabinet width in G 30	944065 30
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F