

Garant GRIDLINE

Base cabinet with drawer, Plain sheet metal swing doors, 36×16G, Height: 800mm**Order data**

Order number	940101 800
GTIN	4062406068646
Item class	9GI

Description**Version:**

Equipped cabinet in 40×20G, with drawers 36×16G.

Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	1000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Weight	54 kg
ComfortClose	no
Depth	500 mm
Electronic locking system can be retrofitted	yes
Cabinet fronts	Plain sheet metal swing door
Usable height	645 mm
Drawer/pull-out shelf load capacity	75 kg
Number of drawers	1
Drawer runner extension (partial/full extension)	100 %
Handle positioning	top
Height	800 mm
Number of shelves	1
Drawer usable depth	400 mm
Drawer usable depth in G	16
Drawer usable width	900 mm
Width in G	40
Drawer usable width in G	36
Depth in G	20
Drawer usable area in G	36×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×16G

Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Cover made of bamboo Dimension in G 40X20	951980 40X20
Cover made of laminated wood Dimension in G 40X20	951985 40X20
Non-slip mats set for drawers,5 pieces Dimension in G 36X16	951885 36X16
Drawer for swing-door cabinets,Width 40G Drawer front height 150 mm	940642 150
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
Inclined shelf for cabinet / compartment width in G 40	940560 40
Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm	940501 750/800
Drawer for swing-door cabinets,Width 40G Drawer front height 200 mm	940642 200
Drawer for swing-door cabinets,Width 40G Drawer front height 75 mm	940642 75
Mat for drawers Dimension in G 36X16	951830 36X16
Extended lighting set for GridLine cabinets withSwing doors, width 40G for cabinet height 750/800 mm	940511 750/800
Drawer for swing-door cabinets,Width 40G Drawer front height 100 mm	940642 100
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Ribbed rubber mat for drawers Dimension in G 36X16	951910 36X16
Storage shelf for cabinet / compartment width in G 40	940550 40
Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 40	958146 40

Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm

940642 125

Storage shelf slotted for cabinet / compartment width in G 40

940552 40

Drawer for swing-door cabinets,Width 40G Drawer front height 300 mm

940642 300