

Garant GRIDLINE

Base cabinet with drawer, Viewing window swing doors, 36×16G, Height: 800mm



Order data

Order number	940103 800
GTIN	4062406068714
Item class	9GI

Description

Version:

Equipped cabinet in 40×20G, with drawers 36×16G.

Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

ComfortClose	no
Drawer runner extension (partial/full extension)	100 %
Electronic locking system can be retrofitted	yes
Number of shelves	1
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width	1000 mm
Handle positioning	top
Cabinet fronts	Viewing window swing door
Height	800 mm
Weight	54 kg
Depth	500 mm
Drawer/pull-out shelf load capacity	75 kg
Number of drawers	1
Usable height	645 mm
Drawer usable depth in G	16
Drawer usable depth	400 mm
Drawer usable width in G	36
Depth in G	20
Width in G	40
Drawer usable width	900 mm
Drawer usable area in G	36×16
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×16G

Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm	940642 125
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Non-slip mats set for drawers,5 pieces Dimension in G 36X16	951885 36X16
Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 40	958146 40
Ribbed rubber mat for drawers Dimension in G 36X16	951910 36X16
Drawer for swing-door cabinets,Width 40G Drawer front height 300 mm	940642 300
Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm	940501 750/800
Cover made of laminated wood Dimension in G 40X20	951985 40X20
Drawer for swing-door cabinets,Width 40G Drawer front height 75 mm	940642 75
Slide handle for GridLine Type GP11	914226 GP11
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Cover made of bamboo Dimension in G 40X20	951980 40X20
Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for swing-door cabinets,Width 40G Drawer front height 200 mm	940642 200
	940642 150

Drawer for swing-door cabinets,Width 40G Drawer front height 150 mm

Inclined shelf for cabinet / compartment width in G 40

940560 40

Drawer for swing-door cabinets,Width 40G Drawer front height 100 mm

940642 100

Extended lighting set for GridLine cabinets withSwing doors, width 40G for cabinet height 750/800 mm

940511 750/800

Mat for drawers Dimension in G 36X16

951830 36X16