

Garant GRIDLINE

Base cabinet with drawer, Roller shutter, 36×14G, Height: 1000mm



Order data

Order number	940109 1000
GTIN	4062406068776
Item class	9GI

Description

Version:

Equipped cabinet in 40×20G, with drawers 36×14G.

Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer bodies RAL 7035 light grey **powder-coated**. Roller shutter of anodised aluminium profiles, colour not configurable.

Doors and drawer fronts RAL 7016 anthracite, **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	64 kg
Drawer runner extension (partial/full extension)	100 %
Width	1000 mm
Usable height	845 mm
ComfortClose	no
Handle positioning	bottom
Number of drawers	1
Height	1000 mm
Cabinet fronts	Roller shutter
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Electronic locking system can be retrofitted	yes
Depth	500 mm
Number of shelves	2
Drawer/pull-out shelf load capacity	75 kg
Width in G	40
Drawer usable depth	350 mm
Drawer usable depth in G	14
Depth in G	20
Drawer usable width	900 mm
Drawer usable width in G	36
Drawer usable area in G	36×14
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable width × usable depth in G	36×14G
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm	940652 300
Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm	940652 150
Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm	940652 200
Cover made of laminated wood Dimension in G 40X20	951985 40X20
Drawer for sliding door cabinets,Width 40G Drawer front height 125 mm	940652 125
Cover made of bamboo Dimension in G 40X20	951980 40X20
Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm	940652 100
Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm	940652 75
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75