

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 750mm**Order data**

Order number	940123 750
GTIN	4062406068905
Item class	9GI

Description**Version:**

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	500 mm
Height	750 mm
Cabinet fronts	Viewing window swing door
Usable height	595 mm

Electronic locking system can be retrofitted	yes
Width	1250 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Weight	70 kg
Handle positioning	top
Number of shelves	1
ComfortClose	no
Depth in G	20
Width in G	50
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 750/800 mm	940510 750/800
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Inclined shelf for cabinet / compartment width in G 50	940560 50

Extended lighting set for GridLine cabinets with Swing doors, width 50G for cabinet height 750/800 mm	940512 750/800
Cover made of bamboo Dimension in G 50X20	951980 50X20
Storage shelf for cabinet / compartment width in G 50	940550 50
Slide handle for GridLine Type GP11	914226 GP11
Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 50	958146 50
Cover made of laminated wood Dimension in G 50X20	951985 50X20