

Garant GRIDLINE

Base cabinet with Plain sheet metal swing doors, Height: 1250mm**Order data**

Order number	940121 1250
GTIN	4062406068875
Item class	9GI

Description**Version:**

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	500 mm
Cabinet fronts	Plain sheet metal swing door

Weight	102 kg
ComfortClose	no
Number of shelves	2
Usable height	1095 mm
Width	1250 mm
Electronic locking system can be retrofitted	yes
Handle positioning	top
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Height	1250 mm
Width in G	50
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm	940510 1000/1250
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Storage shelf slotted for cabinet / compartment width in G 50	940552 50

Slide handle for GridLine Type GP11	914226 GP11
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Storage shelf for cabinet / compartment width in G 50	940550 50
Extended lighting set for GridLine cabinets with Swing doors, width 50G for cabinet height 1000/1250 mm	940512 1000/1250
Inclined shelf for cabinet / compartment width in G 50	940560 50
Cover made of bamboo Dimension in G 50X20	951980 50X20
Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 50	958146 50
Cover made of laminated wood Dimension in G 50X20	951985 50X20