

Garant GRIDLINE

Base cabinet with Viewing window sliding doors, Height: 2000mm



Order data

Order number	940127 2000
GTIN	4062406069100
Item class	9GI

Description

Version:

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Handle positioning	centre
--------------------	--------

Cabinet fronts	Viewing window sliding door
Width	1250 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Weight	156 kg
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Usable height	1845 mm
Width in G	50
Number of shelves	5
Depth	500 mm
Height	2000 mm
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Extended lighting set for GridLine cabinets with Sliding doors, width 50G for cabinet height 2000 mm	940513 2000
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Lock plate for GridLine Type GP21	914227 GP21
	940552 50

Storage shelf slotted for cabinet / compartment width in G 50

Storage shelf for cabinet / compartment width in G 50	940550 50
Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 50	958146 50
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Inclined shelf for cabinet / compartment width in G 50	940560 50