

Garant GRIDLINE

Base cabinet with Viewing window sliding doors, Height: 1250mm**Order data**

Order number	940127 1250
GTIN	4062406069087
Item class	9GI

Description**Version:**

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Handle positioning	top
Weight	102 kg
Cabinet fronts	Viewing window sliding door
Number of shelves	2
ComfortClose	no
Depth	500 mm
Width in G	50
Height	1250 mm
Depth in G	20
Width	1250 mm
Electronic locking system can be retrofitted	yes
Usable height	1095 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Lock plate for GridLine Type GP21	914227 GP21
Cover made of bamboo Dimension in G 50X20	951980 50X20
Extended lighting set for GridLine cabinets with Sliding doors, width 50G for cabinet height 1000/1250 mm	940513 1000/1250
	940590 50

Storage shelf 200 kg for cabinet / compartment width in G 50

Storage shelf for cabinet / compartment width in G 50

940550 50

Cover made of laminated wood Dimension in G 50X20

951985 50X20

Storage shelf slotted for cabinet / compartment width in G 50

940552 50

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F

Base with removable fascia, depth 20G, Height 150 mm
Cabinet casing in G 50

958146 50

Inclined shelf for cabinet / compartment width in G 50

940560 50