

Garant GRIDLINE

## Base cabinet with Plain sheet metal sliding doors, Height: 900mm



### Order data

Order number	940125 900
GTIN	4062406068998
Item class	9GI

### Description

#### Version:

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

#### Supplied with:

Cabinet with storage shelves.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Usable height	745 mm
Height	900 mm

Electronic locking system can be retrofitted	yes
ComfortClose	no
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Handle positioning	top
Depth in G	20
Weight	78 kg
Cabinet fronts	Plain sheet metal sliding door
Number of shelves	1
Width in G	50
Depth	500 mm
Width	1250 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Cover made of bamboo Dimension in G 50X20	951980 50X20
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Cover made of laminated wood Dimension in G 50X20	951985 50X20
Extended lighting set for GridLine cabinets with Sliding doors, width 50G for cabinet height 900 mm	940513 900
Storage shelf for cabinet / compartment width in G 50	940550 50

Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 50	958146 50
Lock plate for GridLine Type GP21	914227 GP21
Inclined shelf for cabinet / compartment width in G 50	940560 50
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Storage shelf slotted for cabinet / compartment width in G 50	940552 50