

Garant GRIDLINE

**Top-mounted cabinet with Viewing window swing doors, Height: 750mm****Order data**

Order number	940133 750
GTIN	4062406069155
Item class	9GI

**Description****Version:**

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Width	1250 mm
Height	750 mm
Weight	70 kg
Cabinet fronts	Viewing window swing door

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Electronic locking system can be retrofitted	yes
Handle positioning	bottom
ComfortClose	no
Number of shelves	1
Depth	500 mm
Usable height	595 mm
Depth in G	20
Width in G	50
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

## Accessories

Slide handle for GridLine Type GP11	914226 GP11
Inclined shelf for cabinet / compartment width in G 50	940560 50
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 750/800 mm	940510 750/800
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
	940512 750/800

Extended lighting set for GridLine cabinets with Swing doors, width 50G for cabinet height 750/800 mm

Storage shelf for cabinet / compartment width in G 50

940550 50

Storage shelf 200 kg for cabinet / compartment width in G 50

940590 50