

Garant GRIDLINE

**Top-mounted cabinet with Viewing window swing doors, Height: 1000mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 940133 1000   |
| GTIN         | 4062406069162 |
| Item class   | 9GI           |

**Description****Version:**

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

|                    |         |
|--------------------|---------|
| Height             | 1000 mm |
| ComfortClose       | no      |
| Handle positioning | bottom  |

|   |  |
|---|--|
| Usable height   | 845 mm   |
| Weight  | 89 kg  |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg   |
| Width   | 1250 mm  |
| Electronic locking system can be retrofitted                    | yes  |
| Number of shelves   | 2  |
| Depth   | 500 mm   |
| Cabinet fronts  | Viewing window swing door                                      |
| Depth in G  | 20   |
| Width in G  | 50   |
| Material thickness  | 0.9 mm   |
| Cabinet housing internal load capacity                          | 1000 kg  |
| Door opening angle  | 250 degrees  |
| Height adjustment interval                                      | 25 mm  |
| Cylinder lock   | modular barrel   |
| Colour selection  | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet   | Add-on cabinet   |
| Type of product   | Cabinet with shelves   |

## Accessories

|   |                  |
|---|------------------|
| Inclined shelf for cabinet / compartment width in G 50        | 940560 50        |
| Slide handle for GridLine Type GP11                           | 914226 GP11      |
| Storage shelf 200 kg for cabinet / compartment width in G 50  | 940590 50        |
| Storage shelf slotted for cabinet / compartment width in G 50 | 940552 50        |
|   | 940512 1000/1250 |

Extended lighting set for GridLine cabinets with Swing doors, width 50G for cabinet height 1000/1250 mm

Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm

940510 1000/1250

Storage shelf for cabinet / compartment width in G 50

940550 50

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F