

Garant GRIDLINE

Top-mounted cabinet with Plain sheet metal sliding doors, Height: 750mm**Order data**

Order number	940135 750
GTIN	4062406069186
Item class	9GI

Description**Version:**

Equipped cabinet in 50×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Cabinet fronts	Plain sheet metal sliding door
Number of shelves	1
Width	1250 mm

Weight	70 kg
Depth in G	20
Depth	500 mm
Handle positioning	bottom
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Height	750 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Usable height	595 mm
Width in G	50
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Storage shelf for cabinet / compartment width in G 50	940550 50
Storage shelf 200 kg for cabinet / compartment width in G 50	940590 50
Storage shelf slotted for cabinet / compartment width in G 50	940552 50
Lock plate for GridLine Type GP21	914227 GP21
	940513 750/800

Extended lighting set for GridLine cabinets with Sliding doors, width 50G for cabinet height 750/800 mm

Inclined shelf for cabinet / compartment width in G 50

940560 50