

## Garant

Side milling cutter with collar Width  $a_p = 12$  mm,  $\varnothing D$ : 125Lmm



### Order data

Order number	218567 125L
GTIN	4045197707536
Item class	210

### Description

**Version:**

Side milling cutters of robust special steel for reduced vibration.

**Application:**

For milling grooves and slots. For flat or non-flat slot base.

**Spare part:**

No. 219984 (TX15; 2.2 Nm).

**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size IP15**.

Side milling cutters available up to  $\varnothing D = 200$  mm.

### Technical description

suitable indexable insert	SNHX
Overall length $L_{tot}$	50 mm
maximum cutting depth $a_{e\max}$	29.7 mm
Number of effective inserts $Z_{eff}$	6
Cutting edge $\varnothing D_c$	125 mm

Collar Ø d <sub>1</sub>	59 mm
Mounting bore Ø	32 mm
Number of indexable inserts	12
Shank type	with bore
Through-coolant	no
Tool exchange	PowerCard
ISO code indexable insert	SN.. 1207
Pack of insert screws	219984 (IP15; 2.2 Nm)
Type of product	Side milling cutter

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2
Set of insert screws 10-piece	219984