

Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 1500mm



Order data

Order number	940165 1500
GTIN	4062406069742
Item class	9GI

Description

Version:

Equipped cabinet in 60×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

ComfortClose	no
--------------	----

Cabinet fronts	Plain sheet metal sliding door
Height	1500 mm
Width	1500 mm
Depth in G	20
Usable height	1363 mm
Handle positioning	top
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Depth	500 mm
Electronic locking system can be retrofitted	yes
Weight	135 kg
Number of shelves	6
Width in G	60
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm	940651 200
Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 60	958146 60
Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm	940651 150

Inclined shelf for cabinet / compartment width in G 30	940560 30
Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm	940651 75
Cover made of laminated wood Dimension in G 60X20	951985 60X20
Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm	940651 125
Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm	940651 100
Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm	940651 300
Cover made of bamboo Dimension in G 60X20	951980 60X20
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30
Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 1500 mm	940514 1500
Storage shelf for cabinet / compartment width in G 30	940550 30
Lock plate for GridLine Type GP21	914227 GP21
Storage shelf slotted for cabinet / compartment width in G 30	940552 30