

Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 750mm**Order data**

Order number	940165 750
GTIN	4062406069599
Item class	9GI

Description**Version:**

Equipped cabinet in 60×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

ComfortClose	no
Depth in G	20
Weight	74 kg
Depth	500 mm

Width in G	60
Width	1500 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Number of shelves	2
Height	750 mm
Usable height	613 mm
Cabinet fronts	Plain sheet metal sliding door
Electronic locking system can be retrofitted	yes
Handle positioning	top
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Inclined shelf for cabinet / compartment width in G 30	940560 30
Base with removable fascia, depth 20G, Height 150 mm Cabinet casing in G 60	958146 60
Cover made of bamboo Dimension in G 60X20	951980 60X20
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Lock plate for GridLine Type GP21	914227 GP21
Storage shelf for cabinet / compartment width in G 30	940550 30
Drawer for sliding door cabinets, Width 30G Drawer front height 100 mm	940651 100

Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm	940651 75
Cover made of laminated wood Dimension in G 60X20	951985 60X20
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30
Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm	940651 150
Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm	940651 300
Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 750/800 mm	940514 750/800
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm	940651 200
Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm	940651 125