

Garant GRIDLINE

**Base cabinet with Plain sheet metal sliding doors, Height: 800mm****Order data**

Order number	940165 800
GTIN	4062406069605
Item class	9GI

**Description****Version:**

Equipped cabinet in 60×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Usable height	663 mm
ComfortClose	no
Width in G	60
Cabinet fronts	Plain sheet metal sliding door

Depth	500 mm
Handle positioning	top
Electronic locking system can be retrofitted	yes
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Height	800 mm
Width	1500 mm
Weight	77 kg
Depth in G	20
Number of shelves	2
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Cover made of bamboo Dimension in G 60X20	951980 60X20
Cover made of laminated wood Dimension in G 60X20	951985 60X20
Inclined shelf for cabinet / compartment width in G 30	940560 30
Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 750/800 mm	940514 750/800
	940651 75

Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm

Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm

940651 100

Base with removable fascia, depth 20G,Height 150 mm  
Cabinet casing in G 60

958146 60

Storage shelf for cabinet / compartment width in G 30

940550 30

Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm

940651 125

Storage shelf200 kg for cabinet / compartment width in G 30

940590 30

Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm

940651 300

Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm

940651 200

Lock plate for GridLine Type GP21

914227 GP21

Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm

940651 150