

Garant GRIDLINE

Top-mounted cabinet with Viewing window sliding doors, Height: 750mm**Order data**

Order number	940177 750
GTIN	4062406069872
Item class	9GI

Description**Version:**

Equipped cabinet in 60×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width in G	60
Usable height	613 mm
Cabinet fronts	Viewing window sliding door
Depth	500 mm

Height	750 mm
ComfortClose	no
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width	1500 mm
Handle positioning	bottom
Number of shelves	2
Weight	74 kg
Depth in G	20
Electronic locking system can be retrofitted	yes
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm	940651 150
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Lock plate for GridLine Type GP21	914227 GP21
Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm	940651 100
Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm	940651 75
	940514 750/800

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 750/800 mm

Storage shelf 200 kg for cabinet / compartment width in G 30

940590 30

Drawer for sliding door cabinets, Width 30G Drawer front height 200 mm

940651 200

Drawer for sliding door cabinets, Width 30G Drawer front height 125 mm

940651 125

Storage shelf for cabinet / compartment width in G 30

940550 30

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F

Inclined shelf for cabinet / compartment width in G 30

940560 30

Drawer for sliding door cabinets, Width 30G Drawer front height 300 mm

940651 300