

Garant GRIDLINE

Top-mounted cabinet with Plain sheet metal sliding doors, Height: 750mm



Order data

Order number	940175 750
GTIN	4062406069841
Item class	9GI

Description

Version:

Equipped cabinet in 60×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Cabinet fronts	Plain sheet metal sliding door
Usable height	613 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg

Width in G	60
Depth in G	20
Handle positioning	bottom
Height	750 mm
Electronic locking system can be retrofitted	yes
ComfortClose	no
Number of shelves	2
Width	1500 mm
Weight	74 kg
Depth	500 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Inclined shelf for cabinet / compartment width in G 30	940560 30
Storage shelf for cabinet / compartment width in G 30	940550 30
Drawer for sliding door cabinets, Width 30G Drawer front height 200 mm	940651 200
Drawer for sliding door cabinets, Width 30G Drawer front height 150 mm	940651 150

Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm	940651 125
Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm	940651 75
Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 750/800 mm	940514 750/800
Lock plate for GridLine Type GP21	914227 GP21
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm	940651 100
Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm	940651 300