

Garant GRIDLINE

Base cabinet with Viewing window sliding doors, Height: 2000mm



Order data

Order number	940167 2000
GTIN	4062406069827
Item class	9GI

Description

Version:

Equipped cabinet in 60×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	20
------------	----

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Handle positioning	centre
ComfortClose	no
Cabinet fronts	Viewing window sliding door
Width	1500 mm
Electronic locking system can be retrofitted	yes
Number of shelves	10
Depth	500 mm
Height	2000 mm
Usable height	1863 mm
Width in G	60
Weight	171 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Drawer for sliding door cabinets, Width 30G Drawer front height 150 mm	940651 150
Lock plate for GridLine Type GP21	914227 GP21
	940651 125

Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm

Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm

940651 75

Shelf clip set for GridLine cabinets20 pieces Type F

940559 F

Storage shelf for cabinet / compartment width in G 30

940550 30

Inclined shelf for cabinet / compartment width in G 30

940560 30

Storage shelf slotted for cabinet / compartment width in G 30

940552 30

Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm

940651 100

Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm

940651 200

Base with removable fascia, depth 20G,Height 150 mm
Cabinet casing in G 60

958146 60

Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm

940651 300

Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 2000 mm

940514 2000