

Garant GRIDLINE

**Base cabinet with drawer, Plain sheet metal sliding doors, 26×14G, Height: 1500mm****Order data**

Order number	940185 1500
GTIN	4062406066987
Item class	9GI

**Description****Version:**

Equipped cabinet in 60×20G, with drawers 26×14G. Mountings for shelves at 25mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

**Supplied with:**

Cabinet with shelves and drawers.

**Colour:**

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Drawer usable width in G	26
Width	1500 mm
Number of drawers	2
Handle positioning	top
Number of shelves	6
Width in G	60
Drawer/pull-out shelf load capacity	75 kg
ComfortClose	no
Drawer runner extension (partial/full extension)	100 %
Usable height	1363 mm
Drawer usable depth in G	14
Electronic locking system can be retrofitted	yes
Depth	500 mm
Drawer usable area in G	26×14
Weight	147 kg
Depth in G	20
Height	1500 mm
Drawer usable width	650 mm
Drawer usable depth	350 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×14G
Type of cabinet	Base cabinet

Type of product

Cabinet with shelves

## Accessories

Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm

940651 125

Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm

940651 150

Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm

940651 300

Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 1500 mm

940514 1500

Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm

940651 100

Base with removable fascia, depth 20G,Height 150 mm  
Cabinet casing in G 60

958146 60

Cover made of laminated wood Dimension in G 60X20

951985 60X20

Comfort Close drawer closure damping system Load capacity of the drawer 75 kg

950180 75

Storage shelf slotted for cabinet / compartment width in G 30

940552 30

Inclined shelf for cabinet / compartment width in G 30

940560 30

Cover made of bamboo Dimension in G 60X20

951980 60X20

Storage shelf200 kg for cabinet / compartment width in G 30

940590 30

Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm

940651 75

Lock plate for GridLine Type GP21

914227 GP21

Storage shelf for cabinet / compartment width in G 30

940550 30

Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm

940651 200