

Garant GRIDLINE

Base cabinet with drawer, Plain sheet metal sliding doors, 26×14G, Height: 2000mm**Order data**

Order number	940185 2000
GTIN	4062406066994
Item class	9GI

Description**Version:**

Equipped cabinet in 60×20G, with drawers 26×14G. Mountings for shelves at 25mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Number of drawers	3
Drawer usable depth	350 mm
Electronic locking system can be retrofitted	yes
Depth in G	20
Usable height	1863 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
ComfortClose	no
Drawer usable width	650 mm
Handle positioning	centre
Drawer/pull-out shelf load capacity	75 kg
Drawer usable area in G	26×14
Width in G	60
Depth	500 mm
Width	1500 mm
Drawer usable width in G	26
Drawer runner extension (partial/full extension)	100 %
Weight	178 kg
Height	2000 mm
Number of shelves	8
Drawer usable depth in G	14
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×14G
Type of cabinet	Base cabinet

Type of product

Cabinet with shelves

Accessories

Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm

940651 300

Lock plate for GridLine Type GP21

914227 GP21

Storage shelf200 kg for cabinet / compartment width in G 30

940590 30

Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm

940651 125

Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 2000 mm

940514 2000

Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm

940651 200

Inclined shelf for cabinet / compartment width in G 30

940560 30

Comfort Close drawer closure damping system Load capacity of the drawer 75 kg

950180 75

Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 60

958146 60

Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm

940651 75

Storage shelf for cabinet / compartment width in G 30

940550 30

Storage shelf slotted for cabinet / compartment width in G 30

940552 30

Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm

940651 100

Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm

940651 150