

Garant GRIDLINE

**Base cabinet with drawer, Plain sheet metal sliding doors, 26×14G, Height: 1000mm****Order data**

Order number	940185 1000
GTIN	4062406066963
Item class	9GI

**Description****Version:**

Equipped cabinet in 60×20G, with drawers 26×14G. Mountings for shelves at 25mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

**Supplied with:**

Cabinet with shelves and drawers.

**Colour:**

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Usable height	863 mm
Height	1000 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable width in G	26
Depth	500 mm
Width in G	60
Drawer usable area in G	26×14
Drawer runner extension (partial/full extension)	100 %
Drawer usable width	650 mm
Drawer usable depth in G	14
Depth in G	20
Handle positioning	top
Electronic locking system can be retrofitted	yes
Weight	109 kg
Width	1500 mm
Number of shelves	4
Drawer usable depth	350 mm
ComfortClose	no
Number of drawers	2
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×14G
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Cover made of laminated wood Dimension in G 60X20	951985 60X20
Cover made of bamboo Dimension in G 60X20	951980 60X20
Inclined shelf for cabinet / compartment width in G 30	940560 30
Drawer for sliding door cabinets,Width 30G Drawer front height 100 mm	940651 100
Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 60	958146 60
Drawer for sliding door cabinets,Width 30G Drawer front height 200 mm	940651 200
Drawer for sliding door cabinets,Width 30G Drawer front height 300 mm	940651 300
Lock plate for GridLine Type GP21	914227 GP21
Storage shelf for cabinet / compartment width in G 30	940550 30
Drawer for sliding door cabinets,Width 30G Drawer front height 150 mm	940651 150
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30
Drawer for sliding door cabinets,Width 30G Drawer front height 75 mm	940651 75
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 1000/1250 mm	940514 1000/1250
Drawer for sliding door cabinets,Width 30G Drawer front height 125 mm	940651 125