

Garant GRIDLINE

**Top-mounted cabinet with drawer, Viewing window sliding doors, 26×14G,
Height: 750mm****Order data**

Order number	940197 750
GTIN	4062406069995
Item class	9GI

Description**Version:**

Equipped cabinet in 60×20G, with drawers 26×14G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	1500 mm
Weight	90 kg

Drawer usable depth	350 mm
Drawer/pull-out shelf load capacity	75 kg
Number of drawers	2
Handle positioning	bottom
ComfortClose	no
Depth	500 mm
Drawer runner extension (partial/full extension)	100 %
Electronic locking system can be retrofitted	yes
Drawer usable width in G	26
Drawer usable width	650 mm
Drawer usable depth in G	14
Height	750 mm
Number of shelves	2
Usable height	613 mm
Depth in G	20
Drawer usable area in G	26×14
Width in G	60
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×14G
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Comfort Close drawer closure damping system Load
capacity of the drawer 75 kg

950180 75