

Garant GRIDLINE

Base cabinet with Plain sheet metal sliding doors, Height: 2000mm**Order data**

Order number	940205 2000
GTIN	4062406070076
Item class	9GI

Description**Version:**

Equipped cabinet in 80×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	1863 mm
---------------	---------

Width in G	80
Electronic locking system can be retrofitted	yes
Width	2000 mm
Height	2000 mm
Depth	500 mm
Cabinet fronts	Plain sheet metal sliding door
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Depth in G	20
Number of shelves	10
Handle positioning	centre
Weight	195 kg
ComfortClose	no
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm	940652 100
Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm	940652 150
Lock plate for GridLine Type GP21	914227 GP21
	958146 80

Base with removable fascia, depth 20G, Height 150 mm
Cabinet casing in G 80

Inclined shelf for cabinet / compartment width in G 40

940560 40

Shelf clip set for GridLine cabinets 20 pieces Type F

940559 F

Drawer for sliding door cabinets, Width 40G Drawer front height 125 mm

940652 125

Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 2000 mm

940515 2000

Storage shelf slotted for cabinet / compartment width in G 40

940552 40

Storage shelf 200 kg for cabinet / compartment width in G 40

940590 40

Drawer for sliding door cabinets, Width 40G Drawer front height 75 mm

940652 75

Storage shelf for cabinet / compartment width in G 40

940550 40

Drawer for sliding door cabinets, Width 40G Drawer front height 200 mm

940652 200

Drawer for sliding door cabinets, Width 40G Drawer front height 300 mm

940652 300