

Garant GRIDLINE

Base cabinet with Viewing window sliding doors, Height: 1500mm**Order data**

Order number	940207 1500
GTIN	4062406070137
Item class	9GI

Description**Version:**

Equipped cabinet in 80×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	1500 mm
Usable height	1363 mm

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Width in G	80
Handle positioning	top
ComfortClose	no
Cabinet fronts	Viewing window sliding door
Number of shelves	6
Depth in G	20
Depth	500 mm
Width	2000 mm
Electronic locking system can be retrofitted	yes
Weight	151 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm	940652 75
Cover made of laminated wood Dimension in G 80X20	951985 80X20
Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm	940652 200
	940652 300

Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm

Extended lighting set for GridLine cabinets withSliding doors, width 80G for cabinet height 1500 mm

940515 1500

Storage shelf200 kg for cabinet / compartment width in G 40

940590 40

Storage shelf slotted for cabinet / compartment width in G 40

940552 40

Inclined shelf for cabinet / compartment width in G 40

940560 40

Lock plate for GridLine Type GP21

914227 GP21

Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm

940652 100

Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm

940652 150

Drawer for sliding door cabinets,Width 40G Drawer front height 125 mm

940652 125

Shelf clip set for GridLine cabinets20 pieces Type F

940559 F

Cover made of bamboo Dimension in G 80X20

951980 80X20

Base with removable fascia, depth 20G,Height 150 mm
Cabinet casing in G 80

958146 80