

Garant GRIDLINE

**Base cabinet with Viewing window sliding doors, Height: 1000mm****Order data**

Order number	940207 1000
GTIN	4062406070113
Item class	9GI

**Description****Version:**

Equipped cabinet in 80×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Usable height	863 mm
ComfortClose	no
Cabinet fronts	Viewing window sliding door
Width in G	80

Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Weight	114 kg
Height	1000 mm
Number of shelves	4
Electronic locking system can be retrofitted	yes
Width	2000 mm
Depth	500 mm
Handle positioning	top
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Cover made of bamboo Dimension in G 80X20	951980 80X20
Drawer for sliding door cabinets,Width 40G Drawer front height 125 mm	940652 125
Lock plate for GridLine Type GP21	914227 GP21
Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm	940652 150
Extended lighting set for GridLine cabinets withSliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250
Storage shelf slotted for cabinet / compartment width in G 40	940552 40

Base with removable fascia, depth 20G,Height 150 mm Cabinet casing in G 80	958146 80
Storage shelf for cabinet / compartment width in G 40	940550 40
Inclined shelf for cabinet / compartment width in G 40	940560 40
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm	940652 75
Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm	940652 100
Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm	940652 300
Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm	940652 200
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
Cover made of laminated wood Dimension in G 80X20	951985 80X20