

Garant GRIDLINE

Base cabinet with drawer, Plain sheet metal sliding doors, 36×14G, Height: 2000mm**Order data**

Order number	940225 2000
GTIN	4062406070274
Item class	9GI

Description**Version:**

Equipped cabinet in 80×20G, with drawers 36×14G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	211 kg
Handle positioning	centre
Drawer runner extension (partial/full extension)	100 %
Height	2000 mm
Drawer usable depth	350 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Depth in G	20
Drawer usable depth in G	14
Depth	500 mm
ComfortClose	no
Drawer usable area in G	36×14
Width in G	80
Width	2000 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable width	900 mm
Drawer usable width in G	36
Electronic locking system can be retrofitted	yes
Usable height	1863 mm
Number of drawers	3
Number of shelves	8
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×14G
Type of product	Cabinet with shelves

Accessories

Drawer for sliding door cabinets,Width 40G Drawer front height 125 mm	940652 125
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm	940652 200
Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm	940652 75
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
Extended lighting set for GridLine cabinets withSliding doors, width 80G for cabinet height 2000 mm	940515 2000
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm	940652 300
Inclined shelf for cabinet / compartment width in G 40	940560 40
Lock plate for GridLine Type GP21	914227 GP21
Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm	940652 100
Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm	940652 150