

Garant GRIDLINE

Top-mounted cabinet with Viewing window sliding doors, Height: 1000mm



Order data

Order number	940217 1000
GTIN	4062406070205
Item class	9GI

Description

Version:

Equipped cabinet in 80×20G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	20
Cabinet fronts	Viewing window sliding door
Weight	114 kg
Usable height	863 mm

Height	1000 mm
ComfortClose	no
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Handle positioning	bottom
Depth	500 mm
Width in G	80
Electronic locking system can be retrofitted	yes
Width	2000 mm
Number of shelves	4
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm	940652 150
Extended lighting set for GridLine cabinets withSliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250
Inclined shelf for cabinet / compartment width in G 40	940560 40
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
	940652 125

Drawer for sliding door cabinets,Width 40G Drawer front height 125 mm

Storage shelf for cabinet / compartment width in G 40

940550 40

Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm

940652 75

Shelf clip set for GridLine cabinets20 pieces Type F

940559 F

Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm

940652 100

Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm

940652 300

Lock plate for GridLine Type GP21

914227 GP21

Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm

940652 200