

Garant GRIDLINE

Base cabinet with drawer, Viewing window sliding doors, 36×14G, Height: 1250mm



Order data

Order number	940227 1250
GTIN	4062406070328
Item class	9GI

Description

Version:

Equipped cabinet in 80×20G, with drawers 36×14G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Drawer usable area in G	36×14
-------------------------	-------

Number of shelves	4
Drawer usable width	900 mm
Weight	144 kg
Depth in G	20
Drawer usable depth in G	14
Depth	500 mm
Width	2000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Drawer usable width in G	36
Width in G	80
Handle positioning	top
Electronic locking system can be retrofitted	yes
Drawer/pull-out shelf load capacity	75 kg
Height	1250 mm
Usable height	1113 mm
Drawer runner extension (partial/full extension)	100 %
Drawer usable depth	350 mm
Number of drawers	2
ComfortClose	no
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×14G
Type of product	Cabinet with shelves

Accessories

Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for sliding door cabinets,Width 40G Drawer front height 300 mm	940652 300
Inclined shelf for cabinet / compartment width in G 40	940560 40
Drawer for sliding door cabinets,Width 40G Drawer front height 200 mm	940652 200
Drawer for sliding door cabinets,Width 40G Drawer front height 125 mm	940652 125
Shelf clip set for GridLine cabinets20 pieces Type F	940559 F
Storage shelf200 kg for cabinet / compartment width in G 40	940590 40
Extended lighting set for GridLine cabinets withSliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250
Drawer for sliding door cabinets,Width 40G Drawer front height 75 mm	940652 75
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Storage shelf slotted for cabinet / compartment width in G 40	940552 40
Drawer for sliding door cabinets,Width 40G Drawer front height 150 mm	940652 150
Lock plate for GridLine Type GP21	914227 GP21
Cover made of laminated wood Dimension in G 80X20	951985 80X20
Cover made of bamboo Dimension in G 80X20	951980 80X20
Drawer for sliding door cabinets,Width 40G Drawer front height 100 mm	940652 100