

Garant GRIDLINE

Base cabinet with plain sheet metal swing doors, Height: 800mm**Order data**

Order number	940801 800
GTIN	4062406070403
Item class	9GI

Description**Version:**

Empty cabinet in 20×20G. Suitable drawers: 16×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

ComfortClose	no
Height	800 mm
Width	500 mm
Width in G	20

Depth	500 mm
Cabinet fronts	Plain sheet metal swing door
Depth in G	20
Electronic locking system can be retrofitted	yes
Handle positioning	top
Usable height	645 mm
Type of cabinet	Base cabinet
Weight	27 kg
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm	940640 100
Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm	940640 150
Storage shelf for cabinet / compartment width in G 20	940550 20
Drawer for swing-door cabinets,Width 20G Drawer front height 300 mm	940640 300
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm	940640 125

Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm	940640 75
Storage shelf slotted for cabinet / compartment width in G 20	940552 20
Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm	940501 750/800
Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm	940640 200
Inclined shelf for cabinet / compartment width in G 20	940560 20