

Garant GRIDLINE

Base cabinet with plain sheet metal swing doors, Height: 2000mm



Order data

Order number	940821 2000
GTIN	4062406070571
Item class	9GI

Description

Version:

Empty cabinet in 30×20G. Suitable drawers: 26×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	750 mm
Type of cabinet	Base cabinet
Width in G	30
ComfortClose	no

Depth in G	20
Handle positioning	centre
Weight	71 kg
Depth	500 mm
Usable height	1845 mm
Electronic locking system can be retrofitted	yes
Height	2000 mm
Cabinet fronts	Plain sheet metal swing door
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Slide handle for GridLine Type GP11	914226 GP11
Inclined shelf for cabinet / compartment width in G 30	940560 30
Drawer for swing-door cabinets,Width 30G Drawer front height 125 mm	940641 125
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30
Drawer for swing-door cabinets,Width 30G Drawer front height 75 mm	940641 75
Storage shelf for cabinet / compartment width in G 30	940550 30
	940641 300

Drawer for swing-door cabinets,Width 30G Drawer front height 300 mm

Drawer for swing-door cabinets,Width 30G Drawer front height 100 mm

940641 100

Storage shelf slotted for cabinet / compartment width in G 30

940552 30

Drawer for swing-door cabinets,Width 30G Drawer front height 200 mm

940641 200

Drawer for swing-door cabinets,Width 30G Drawer front height 150 mm

940641 150

Basic lighting set for GridLine cabinets withswing doors for cabinet height 2000 mm

940501 2000

Extended lighting set for GridLine cabinets withSwing doors, width 30G for cabinet height 2000 mm

940510 2000