

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 2000mm



Order data

Order number	940823 2000
GTIN	4062406070649
Item class	9GI

Description

Version:

Empty cabinet in 30×20G. Suitable drawers: 26×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Cabinet fronts	Viewing window swing door
Depth	500 mm
Width	750 mm
Electronic locking system can be retrofitted	yes

Height	2000 mm
Weight	71 kg
Depth in G	20
ComfortClose	no
Usable height	1845 mm
Handle positioning	centre
Width in G	30
Type of cabinet	Base cabinet
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 2000 mm	940510 2000
Storage shelf for cabinet / compartment width in G 30	940550 30
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Drawer for swing-door cabinets, Width 30G Drawer front height 300 mm	940641 300
Drawer for swing-door cabinets, Width 30G Drawer front height 150 mm	940641 150
Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm	940501 2000

Storage shelf 200 kg for cabinet / compartment width in G 30	940590 30
Inclined shelf for cabinet / compartment width in G 30	940560 30
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets, Width 30G Drawer front height 100 mm	940641 100
Drawer for swing-door cabinets, Width 30G Drawer front height 200 mm	940641 200
Drawer for swing-door cabinets, Width 30G Drawer front height 125 mm	940641 125
Drawer for swing-door cabinets, Width 30G Drawer front height 75 mm	940641 75