

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 750mm**Order data**

Order number	940823 750
GTIN	4062406070588
Item class	9GI

Description**Version:**

Empty cabinet in 30×20G. Suitable drawers: 26×16G (please order these separately)
Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Levelling base with adjustable feet to compensate for unevenness in the floor.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	500 mm
Usable height	595 mm
ComfortClose	no
Width in G	30

Type of cabinet	Base cabinet
Cabinet fronts	Viewing window swing door
Handle positioning	top
Width	750 mm
Electronic locking system can be retrofitted	yes
Height	750 mm
Weight	34 kg
Depth in G	20
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Cabinet with shelves

Accessories

Slide handle for GridLine Type GP11	914226 GP11
Inclined shelf for cabinet / compartment width in G 30	940560 30
Drawer for swing-door cabinets,Width 30G Drawer front height 125 mm	940641 125
Extended lighting set for GridLine cabinets withSwing doors, width 30G for cabinet height 750/800 mm	940510 750/800
Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm	940501 750/800
Storage shelf200 kg for cabinet / compartment width in G 30	940590 30

Storage shelf for cabinet / compartment width in G 30	940550 30
Drawer for swing-door cabinets,Width 30G Drawer front height 150 mm	940641 150
Drawer for swing-door cabinets,Width 30G Drawer front height 300 mm	940641 300
Drawer for swing-door cabinets,Width 30G Drawer front height 75 mm	940641 75
Storage shelf slotted for cabinet / compartment width in G 30	940552 30
Drawer for swing-door cabinets,Width 30G Drawer front height 100 mm	940641 100
Drawer for swing-door cabinets,Width 30G Drawer front height 200 mm	940641 200